

Amalgam Separator Flow-Through Models	Maximum Tested Flow Rate (milliliters/minute)
American Dental Accessories Asdex AS-9 (chairside)	500
AB Dental Trends Rasch 890-1000/4000 or 890-6000/4500	4000
AB Dental Trends Rasch 890-1000 or 890-6000	2000
Rebec CatchHg 1000 or 400	1000
SolmeteX Hg5	50
Maximum Separation System 2000	2500
Maximum Separation System 1000	1000

Amalgam Separator Batch-Treatment Models	Storage Capacity (liters)
R&D Services CH 9 The Amalgam Collector (chairside)	2.3
R&D Services CH 12 The Amalgam Collector (chairside)	3.7
R&D Services CE 18 The Amalgam Collector	6.5
R&D Services CE 24 The Amalgam Collector	16.4
DRNA BullfroHg 10	10
Air Techniques Guardian Amalgam Collector	14.8
Air Techniques Guardian Amalgam Collector	29.6
SolmeteX Hg10	95

Models are installed centrally, unless noted otherwise.